

# **Rotovalve Light**



## **Light Duty Rotary Valves**

The **Rotovalve Light** is the solution offered by **Hanningfield** to improve product flow and build-ups in the download phase. The alternating movement of the blades allows for a constant and regular feed, thus avoiding the incorrect mixing of the product.

{xtypo\_info}The **Rotovalve Light** is the ideal solution for loading powder into compression machines, fillers, mills and weighing stations.{/xtypo info}

Thanks to its compartmented design, the **Rotovalve Light** is a volumetric dosage system of the product in the process phase.

{faq inline/tabs}

#### **Profile**

The special clamp that is supplied with the valve (quick open versions) makes it more ergonomic and sto The Rotovalve Light is also available with a satisfied by the light is

#### **Features & Benefits**

- Easy Clean Hygienic Design
- Modular Construction
- Compact Dimensions
- 316L Stainless Steel Contact Parts
- Optional Pneumatic Actuation
- Various Gasket Material Options

## **Technical Specifications**

- Valve body in stainless steel 1.4404 (AISI 316L) or in advanced plastic FDA approved
- Silicone coated disc, FDA approved (CFR 177.2600)
- Gasket in silicone, EPDM, FKM (Viton®) or PTFE: All elastomers are FDA approved (CFR 177.2600) I
- All Components in stainless steel EN 1.4301 (AISI 304)

Finish: inside high polish [Ra < 0,1 microns], outside satin [Ra

- **Drive:** handle or rotary pneumatic actuator

#### **Process Valves Series**

Sterivalve (Hygienic Butterfly Valv



Sterisplit (Split Butterfly Valves)

**Flexivalve** (Flexible Vane Valves)

Rotavalve Light (Light Duty Rotary Valve)

Rotavalve Heavy (Heavy Duty Rotary Valves)

**Gallery** {gallery}rotovalvelight{/gallery}

{/faq}

### **Download Brochure:**

{xtypo\_download} T

<u>Light Duty Rotary&nbsp;Valves (Rotovalve Light)</u> {/xtypo\_download}

